



DATA SHEET

MP 50 / MP 51

Manometer



Easy to use



Manual autozero




Hold function



Auto shut-off: 20 minutes

Features of housing

Material	ABS
Protection	IP54
Display	2 lines, LCD technology, 50 x 36 mm. 1 line of 5 digits with 7 segments (value) 1 line of 5 digits with 16 segments (unit)
Height of digits	Values: 9.2 mm. Units: 4.7 mm
Weight	200 g (with batteries)



Technical specifications

	MP 50	MP 51
Parameter	Differential pressure	Differential pressure
Measuring units	Pa, mmH ₂ O, inWg, daPa	mmH ₂ O, kPa, inWg, mbar, mmHg, daPa
Measuring range	From -1000 to +1000 Pa	From -1000 to +1000 mmH ₂ O
Accuracy ⁽¹⁾	±0.5 % of reading ±2 Pa	±0.5% of reading ±2 mmH ₂ O
Resolution	1 Pa	From -200 to +200 mmH ₂ O: 0.1 mmH ₂ O. Beyond: 1 mmH ₂ O
Response time		T ₆₃ = 0.3 s
Measuring element		Piezoresistive sensor
Conditions of use (°C/%RH/m)		From 0 to +50 °C. In non-condensing conditions. From 0 to 2000 m.
Storage temperature		From -20 to +80 °C
Power supply		4 batteries AAA LR03 1.5 V
Battery life		180 hours

European directives 2014/30/EU EMC; 2014/35/EU Low Voltage; 2011/65/EU RoHS II; 2012/19/EU WEEE

⁽¹⁾ All the accuracies indicated in this technical datasheet were stated in laboratory conditions, and can be guaranteed for measurements carried out in the same conditions, or carried out with calibration compensation.

Kit content

Instruments are supplied with an adjustment certificate, a soft case and 2 x 1 m of silicone tube.

Accessories

Reference	Description
-	Calibration certificate
MT 51	Soft case
CQ 15	Magnetic protective housing



Only the accessories supplied with the device must be used.

Warranty

Instruments have 1-year warranty for any manufacturing defect (return to our After-Sales Service required for appraisal).

Maintenance:

We carry out calibration, adjustment and maintenance of your instruments to guarantee a constant level of quality of your measurements.

As part of Quality Assurance Standards, we recommend you to carry out a yearly checking.

Precautions for use:

Please always use the device in accordance with its intended use and within parameters described in the technical features in order not to compromise the protection ensured by the device.



Uw distributeur
Hitma B.V.

Vragen over handmeters:
www.hitma-handmeters.nl
tel.: +31 (0)36 535 06 51